



Raw Material:PE100 PE100RC PERTII
 Standard:ISO4437-3 ISO4427-3 EN12201-3 ISO22391-3
 SDR9 can be supplied per request.
 Followed parameters are for reference.

| Code | SizeΦ(mm) | SDR | Pcs/Box | L1 | L2 | L3 | L |
|-------------|-----------|-------|---------|-----|-----|-----|------|
| BFT40A | 40 | 11 | 100 | 48 | 48 | 80 | 167 |
| BFT50A | 50 | 11 | 60 | 56 | 56 | 100 | 201 |
| BFT63A/B | 63 | 11/17 | 35 | 63 | 64 | 112 | 227 |
| BFT75A/B | 75 | 11/17 | 24 | 70 | 71 | 133 | 260 |
| BFT90A/B | 90 | 11/17 | 12 | 80 | 80 | 140 | 280 |
| BFT110A/B | 110 | 11/17 | 12 | 83 | 84 | 153 | 303 |
| BFT125A/B | 125 | 11/17 | 6 | 87 | 87 | 161 | 336 |
| BFT140A/B | 140 | 11/17 | 4 | 90 | 90 | 187 | 381 |
| BFT160A/B | 160 | 11/17 | 3 | 101 | 100 | 200 | 385 |
| BFT180A/B | 180 | 11/17 | 2 | 105 | 105 | 213 | 456 |
| BFT200A/B | 200 | 11/17 | 2 | 95 | 107 | 221 | 467 |
| BFT225A/B | 225 | 11/17 | 1 | 124 | 123 | 265 | 533 |
| BFT250A/B | 250 | 11/17 | 1 | 132 | 133 | 285 | 584 |
| BFT280A/B | 280 | 11/17 | 1 | 136 | 136 | 310 | 620 |
| BFT315A1/B1 | 315 | 11/17 | 22 | 84 | 85 | 276 | 539 |
| BFT315A2/B2 | 315 | 11/17 | 22 | 153 | 153 | 344 | 573 |
| BFT355A1/B1 | 355 | 11/17 | 22 | 162 | 105 | 374 | 643 |
| BFT355A2/B2 | 355 | 11/17 | 22 | 165 | 163 | 384 | 766 |
| BFT400A1/B1 | 400 | 11/17 | 18 | 86 | 79 | 340 | 595 |
| BFT400A2/B2 | 400 | 11/17 | 14 | 120 | 120 | 370 | 764 |
| BFT450A/B | 450 | 11/17 | 10 | 127 | 154 | 395 | 815 |
| BFT500A/B | 500 | 11/17 | 8 | 135 | 137 | 420 | 850 |
| BFT560A/B | 560 | 11/17 | 6 | 140 | 138 | 440 | 906 |
| BFT630A/B | 630 | 11/17 | 2 | 140 | 138 | 515 | 1106 |